



QUIDEL

MOLECULAR. SOLUTIONS.



# Solana<sup>®</sup>

*The Accurate. Sustainable.  
Molecular Solution.*



When information from your test relies on:

Accuracy

Quidel's proprietary isothermal helicase-dependent amplification (HDA) with fluorescence detection delivers molecular results you can trust, in an actionable timeframe.

Throughput

Solana's workflow is simple and flexible, capable of testing a single specimen or batching up to 12 tests at a time.

Patient Satisfaction

Providing answers that are accurate and timely to improve patient satisfaction and build trust that they are receiving the highest quality care.

# Solana<sup>®</sup>

Solana provides critical diagnostic information for the following disease states:



## Strep Complete

Pyogenic group C/G strep is a significant cause of strep pharyngitis in teenagers and adults. These strains will go undetected when using a rapid antigen test.

Differentiate between A and the pyogenic C/G strains in just 30 minutes.

**Group A and pyogenic Group C/G with no culture confirmation required.**

## HSV 1+2/VZV

Detect and differentiate Herpes simplex virus type 1, Herpes simplex virus type 2, and Varicella-zoster virus from any lesion in just 60 minutes.

**Remove the uncertainty in your lesion diagnosis.**

## Group A Strep

30 minutes to a confirmatory Strep A diagnosis. Gold standard sensitivity with the ability to run up to 12 specimens in a single run, allowing prompt initiation of patient management and antimicrobial therapy.

**Group A strep testing with no culture confirmation required.**

## Influenza A+B

Highly accurate molecular results in an actionable timeframe. Results you can trust for your high risk patients, on a platform built for your lab in just 45 minutes.

**Results you can trust when accuracy is critical.**

## Trichomonas

The current recommends testing for Trichomonas using highly sensitive Nucleic Acid Amplification Tests, like Solana, to avoid the underdiagnosis and undertreatment of Trichomonas infections.

**Stop compromising. Start treating.**

Test*	Classification	Sensitivity %	Specificity %
Strep Complete	Pyogenes	98.8	98.9
	Dysgalactaie	100	99.5
HSV 1+2/VZV	Cutaneous	100/92.3/100	98.0/92.3/100
	Mucocutaneous	100/99.1/100	100/99.1/100
GAS		98.2	97.2
Influenza A+B		97.2/96.7	96.7/98.9
Trichomonas	Swab	99.2	95.0
	Urine	95.0	98.2

SS2027810EN00 (04/17)



QUIDEL

© 2015 Thermo Fisher Scientific Inc. All rights reserved.  
Trademarks used are owned as indicated at [www.fishersci.com/trademarks](http://www.fishersci.com/trademarks).

\*Refer to each products Package Insert for additional performance claims.

### In the United States:

For customer service, call 1-800-640-0640

To fax an order, use 1-800-290-0290

To order online: [www.fisherhealthcare.com](http://www.fisherhealthcare.com)



**Fisher  
HealthCare**

A Thermo Fisher Scientific Brand