

	Ovation ESC (electronic single channel) and Ovation E8 & E12 (multichannel):	0.5-20µL	2-125µL 5-250µL	25-850 25-1250µL		
	Ovation M5 & Ovation M10 (macro volume):				100-5000µL	0.2-10mL
	Ovation QS (quick-set adjustable volume):	0.2-2µL 1.0-10µL 2.0-20µL	10-100µL 20-200µL	100-1000µL		
	Ovation F1 & Ovation F2 (fixed volume):	1µL to 20µL	21µL to 200µL	201µL to 1000µL		
	All MLA models:		2µL to 200µL	201µL to 1000µL	1mL to 5mL	6mL to 10mL
	TIP SIZE:	MICRO	SMALL	LARGE	5 mL	10 mL
NON-STERILE	VistaRak 192 tips/rack, 5 racks	22-146-350	22-146-351	22-146-352		
	VistaRak, Low Retention 192 tips/rack, 5 racks	22-146-560	22-146-564			
	VistaStak, 192 tips/layer, 5 layers (small size) or 3 layers (micro and large size)	22-146-353	22-146-354	22-146-355		
	Stacked Rack, 200 tips/layer, 5 layers (small size) or 3 layers (large size)		21-341	21-343		
	Stacked Rack, Trace Metal Certified, 200 tips/layer 5 layers (small size) or 3 layers (large size)		21-319-27	21-319-28		
	Box 100 tips/box (5mL) or 35 tips/box (10mL)				21-318-602	
	VistaClear Box 35 tips/box					22-146-310
	VistaBulk™, 1000 tips/bag, or 250 tips/bag (5mL) or 100 tips/bag (10mL)	22-146-630	22-146-636	22-146-643	22-146-302	22-146-321
	Protectainer™ Bulk Pack, 1000 tips (small) or 750 tips (large)		21-341-20	21-343-20		
Econo-Pak™ Bulk Pack, 1000 tips		22-046-533	22-046-534			
STERILE	VistaRak, Sterile, Pyrogen-free, RNase/DNase certified, 192 tips/rack, 5 racks	22-146-356	22-146-357	22-146-358		
	VistaRak, Sterile, Pyrogen-free, Low Retention, RNase/DNase certified, 192 tips/rack, 5 racks	22-146-561	22-146-565			
	VistaClear Box – Sterile, 60 tips/box (5mL) or 35 tips/box (10mL)				22-146-688	22-146-323
	VistaTip™ Individually Wrapped Sterile, 200 tips		21-341-10 ¹	21-343-10 ¹		
VistaTip Individually Wrapped, Sterile, Pyrogen-free, 200 tips		21-343-21 ¹	21-343-22 ¹			
FILTERED	VistaRak, Filtered, Sterile, Pyrogen-free, RNase/DNase certified, 192 tips/rack, 5 racks	22-146-359	22-146-361	22-146-362		
	VistaRak, Filtered, Sterile, Pyrogen-free, Low Retention, RNase/DNase certified, 192 tips/rack, 5 racks	22-146-562 ²	22-146-566			
	VistaClear Box – Filtered, Sterile, Pyrogen-free, RNase/DNase certified, 60 tips/box (5mL) or 35 tips/box (10mL)				22-146-689	22-146-324
	VistaTip Individually Wrapped, Filtered, Sterile, Pyrogen-free, RNase/DNase certified, 50 tips				22-146-304	22-146-325



VistaRak™



VistaStak™



Stacked Rack

Notes:

1. Not for use with Ovation E8 & E12 Multichannel Pipettes.
2. Not for use with Ovation QS or Ovation F2 1µL or 2µL.
3. All 5mL tips are graduated, marked at 0.1mL increments

In the United States:

For customer service, call 1-800-766-7000
To fax an order, use 1-800-926-1166
To order online: www.fishersci.com

In Canada:

For customer service, call 1-800-234-7437
To fax an order, use 1-800-463-2996
To order online: www.fishersci.ca