

# osom<sup>®</sup>

## Answers for Healthcare

Enhancing the patient experience, improving care, and controlling costs are the new rules of engagement in today's healthcare environment. Emphasis on the value of linking patient outcomes and expense management is critical. Healthcare providers understand the need to provide products and services that directly contribute to this new paradigm.

OSOM<sup>®</sup> rapid diagnostics offer you a variety of family and women's health products, that together with our services, deliver unparalleled value. Fast, point-of-care results help reduce follow-up visits, promote education/prevention and allow for more precise treatment.

Together we can improve patient care and lower healthcare costs. Awesome...yes, OSOM<sup>®</sup>



## Family Health

### OSOM® Strep A Test

- ✓ 96% sensitivity; 98% specificity
- ✓ Results in 5 minutes
- ✓ Includes 2 extra tests for QC

**50 TESTS:** #141  
**CPT CODE:** #87880QW

### OSOM® Ultra Strep A Test

- ✓ Sensitivity not statistically different than single swab culture\*
- ✓ Results in 5 minutes
- ✓ Includes 2 extra tests for QC (#149)

**25 TESTS:** #147  
**50 TESTS:** #149  
**CPT CODE:** #87880QW

\*See package insert

### OSOM® Mono Test

- ✓ >99% sensitivity
- ✓ Includes 2 extra tests for QC
- ✓ Results in 5 minutes
- ✓ No age restrictions

**25 TESTS:** #145  
**CPT CODE:** #86308QW

### OSOM® Influenza A&B Test

- ✓ Differentiates between flu A&B
- ✓ Results in 10 minutes
- ✓ Includes 2 extra tests for QC

**25 TESTS:** #190  
**CONTROL SET:** #191  
**CPT CODE:** #87804

### OSOM® H. pylori Test

- ✓ 95.9% sensitivity; 89% specificity
- ✓ Results in 10 minutes
- ✓ Serum, plasma, or whole blood

**25 TESTS:** #175  
**CONTROL SET:** #176  
**CPT CODES:** #86318QW (whole blood) or #86677 (serum or plasma)



## Women's Health

### OSOM® Trichomonas Rapid Test

- ✓ The *only* CLIA-waived rapid Trichomonas test available
- ✓ More sensitive than wet mount
- ✓ Detects antigen; does not require live organisms

**25 TEST KIT:** #181  
**POSITIVE CONTROL SET:** #182  
**CPT CODE:** #87808QW

### OSOM® BVBLUE® Test

- ✓ The *only* CLIA-waived rapid test for Bacterial Vaginosis
- ✓ Detects elevated vaginal fluid sialidase activity
- ✓ 92.8% sensitive vs. gram stain

**25 TEST KIT:** #183  
**CONTROL SET:** #184  
**CPT CODE:** #87905QW

### OSOM® hCG Urine Test

- ✓ One-step simple
- ✓ 25 mIU/mL sensitivity

**50 TESTS:** #101  
**hCG URINE CONTROL SET:** #134  
**CPT CODE:** #81025

### OSOM® hCG Combo Test

- ✓ Increased sensitivity: 10 mIU/mL (serum); 20 mIU/mL (urine)
- ✓ No drop counting pipette

**25 TESTS/KITS:** #124  
**hCG CONTROL SETS:** #138 (serum); #134 (urine)  
**CPT CODES:** #84703 (serum) or #81025 (urine)

### OSOM® Card Pregnancy Test

- ✓ Increased sensitivity: 20 mIU/mL
- ✓ No drop counting pipette

**25 TESTS/KIT:** #102  
**hCG URINE CONTROL SET:** #134  
**CPT CODE:** #81025

**SEKISUI**  
DIAGNOSTICS

#### THE AMERICAS

Sekisui Diagnostics, LLC  
4 Hartwell Place  
Lexington, MA 02421  
Phone: 800 332 1042  
Fax: 800 762 6311  
Email: osomrapidtests@sekisui-dx.com  
ISO 13485 Certified

#### INTERNATIONAL

Sekisui Diagnostics (UK) Limited  
50 Gibson Drive  
Kings Hill, West Malling  
Kent, ME19 4AF, UK  
Phone: +44 (0) 1732 220022  
Fax: +44 (0) 1732 220024  
Email: info@sekisui-dx.com  
ISO 9001 Certified  
ISO 13485 Certified