

Fisher Scientific accumet[®] AP110, AP115 and AP125 Waterproof Portable Meters

Accurate measurements any time, anywhere

Specifications



- » Large LCD with backlighting and plain-language text – easy to view and use
- » Improved rugged waterproof IP67 housing
- » 0.001 pH resolution and date/ time to meet GLP (AP115, AP125)
- » 200 data point internal memory
- » 3-year meter warranty 1-year electrode warranty

Go Portable! Indoor or outdoor these new accumet meters are versatile and rugged enough for the most demanding applications. Soft touch keys with comfort grip make one-handed operation a breeze.

pecifications			
Model	AP110	AP115	AP125
pH			
Range	- 2.00 to 20.00	- 2.00 to 20.000	- 2.00 to 20.000
Resolution	0.1 / 0.01	0.1 / 0.01 / 0.001	0.1 / 0.01 / 0.001
Accuracy	± 0.01	± 0.002	± 0.002
Calibration points		Up to 6 points	
Available Calibration Values	USA: 2.00, 4.00, 7.00, 10.00, 12.00 NIST: 1.68, 4.01, 6.86, 9.18, 12.45 EURO: 1.00, 3.00, 6.00, 8.00, 10.00, 13.00		
Ion Concentration			
Range	-	-	0.001 to 99,999
Resolution	-	_	1, 2, or 3 significant digits
Accuracy	-	-	0.5 % FS (monovalent) 1 % FS (trivalent)
Calibration points	-	-	2 to 5 points
Available Calibration Values	-	-	0.1, 0.5, 1, 2, 5, 10, 50, 100, 500, 1000
mV, Relative mV			
Range		± 2000	
Resolution	0.1 / 1		
Accuracy		± 0.2 / 2	
Calibration points	1 (Rel mV)		
Available Calibration Values	1 point adjustment		
Temperature °C			
Range	-5 to 100		
Resolution	0.1		
Accuracy	± 0.3		
Calibration points	1 (ATC) & 1 (MTC)		
Available	1 point ± 5 adjustment (ATC),		
Calibration Values	- 5 to 100 default adjustment (MTC)		
Date/Time GLP	NO	YES	YES

* FREE GIFT with purchase – details on back

Meters are small enough for a shirt pocket, yet smart enough for any laboratory. The AP100 kits include an unbreakable accumet pH/temperature electrode that is refillable for a fast response and the longest life. The AP125 accepts any ion selective electrode (ISE) with a BNC connection for direct ion concentration measurement from 0.001 to 99,999 ppm.

F) Fisher Scientific



Ordering Information

Cat. No.	Description
13-636-AP125	AP125 pH/mV/Ion/Temp Meter Kit
13-636-AP125A	AP125 pH/mV/Ion/Temp Meter Only
13-636-AP115	AP115 pH/mV/Temp Advanced Meter Kit
13-636-AP115A	AP115 pH/mV/Temp Advanced Meter Kit
13-636-AP110	AP110 pH/mV/Temp Meter Kit
13-636-AP110A	AP110 pH/mV/Temp Meter Kit
13-636-100	Optional 110 / 220 VAC Power Adapter

Meter Only – includes meter, 9V battery and manual.

Meter Kit – includes meter, combination refillable pH/ATC electrode (13-620-AP50A), refilling solution, hard carrying case, sample bottles, pH calibration packets, 9V battery and manual.

SPECIAL OFFER –

Get a FREE Fisher Scientific Lunch Cooler with any AP100 purchase!



of your invoice or packing slip to claim your gift.				
Contact Name:				

Fill out the form below and fax it to 978-232-1042 along with a copy

Company Name:

Address:

Telephone:

E-mail:

Offer expires December 31, 2008. Please allow 4-6 weeks for delivery of product.

P-FIAP110-E RevA 0608



For customer service, call 1-800-766-7000. To fax an order, use 1-800-926-1166. To order online: www.fishersci.com

3N0625083