

# Durable Insulated Containers

## FOR LABORATORY AND FIELD APPLICATIONS

- Mobile, non-electrical low temperature maintenance, ideal for demanding cryogenic and laboratory testing, as well as dry ice storage and the transport of temperature-sensitive specimens
- Realize years of re-use in the most rugged environments, driving high returns on your investment
- Rugged polyethylene interior and exterior casings and urethane foam insulation
- Rounded interior corners for easy clean-up



MODEL	DIMENSIONS L x W x H (in)		EMPTY WEIGHT (lb)	CAPACITY				HARDWARE/HANDLING ACCESSORIES
	INNER	OUTER		VOL (ft <sup>3</sup> )	DRY ICE CAPACITY (lb)*	WALL THICKNESS (in)	AVG HOLD TIME (days)*	
1167613	11 <sup>5</sup> / <sub>16</sub> x 10 <sup>3</sup> / <sub>8</sub> x 10 <sup>1</sup> / <sub>4</sub>	15 x 14 <sup>1</sup> / <sub>16</sub> x 13 <sup>1</sup> / <sub>2</sub>	12	0.7	50	1 <sup>3</sup> / <sub>4</sub>	7	Opt. carrying strap
0353041	11 <sup>5</sup> / <sub>16</sub> x 10 <sup>3</sup> / <sub>8</sub> x 10 <sup>1</sup> / <sub>4</sub>	15 x 14 <sup>1</sup> / <sub>16</sub> x 21	12	0.7	50	1 <sup>3</sup> / <sub>4</sub>	7	Lid hinge w/ 2 latches; carrying handle
0353027	16 <sup>11</sup> / <sub>16</sub> x 10 <sup>1</sup> / <sub>4</sub> x 10 <sup>1</sup> / <sub>2</sub>	21 <sup>15</sup> / <sub>16</sub> x 14 <sup>7</sup> / <sub>8</sub> x 13 <sup>5</sup> / <sub>8</sub>	16	1.0	80	2 <sup>1</sup> / <sub>4</sub>	10	Lid hinge w/ stay; 2 latches; carrying handle
1167639	15 <sup>5</sup> / <sub>8</sub> x 13 <sup>3</sup> / <sub>4</sub> x 12 <sup>5</sup> / <sub>8</sub>	19 <sup>7</sup> / <sub>8</sub> x 18 <sup>5</sup> / <sub>8</sub> x 16 <sup>5</sup> / <sub>8</sub>	27	1.5	85	2	6	Lid hinge w/ stay; 2 latches; 2 spring loaded handles
22024802	17 x 16 <sup>1</sup> / <sub>2</sub> x 16 <sup>3</sup> / <sub>8</sub>	23 <sup>3</sup> / <sub>8</sub> x 22 <sup>1</sup> / <sub>8</sub> x 21 <sup>1</sup> / <sub>4</sub>	34	2.7	150	2 <sup>1</sup> / <sub>4</sub>	7	Lid hinge w/ stay; 2 latches; opt. dolly
1167611	17 x 16 <sup>1</sup> / <sub>2</sub> x 16 <sup>3</sup> / <sub>8</sub>	23 <sup>3</sup> / <sub>8</sub> x 22 <sup>1</sup> / <sub>8</sub> x 21 <sup>1</sup> / <sub>4</sub>	35	2.7	150	2 <sup>1</sup> / <sub>4</sub>	7	Lid hinge w/ stay; 2 latches; 2 spring loaded handles; opt. dolly
1167620	22 <sup>13</sup> / <sub>16</sub> x 13 <sup>1</sup> / <sub>2</sub> x 21	28 <sup>7</sup> / <sub>8</sub> x 19 <sup>1</sup> / <sub>8</sub> x 25 <sup>1</sup> / <sub>4</sub>	39	3.75	200	2	12	Lid hinge w/ stay; 2 latches; opt. dolly
035252	22 <sup>13</sup> / <sub>16</sub> x 13 <sup>1</sup> / <sub>2</sub> x 21	28 <sup>7</sup> / <sub>8</sub> x 19 <sup>1</sup> / <sub>8</sub> x 25 <sup>1</sup> / <sub>4</sub>	40	3.75	200	2	12	Lid hinge w/ stay; 2 latches; 2 spring loaded handles; opt. dolly

\* Weight calculated using pelletized dry ice  
+ Average time before sublimation

© 2016 Thermo Fisher Scientific Inc. All rights reserved.  
Trademarks used are owned as indicated at [www.fishersci.com/trademarks](http://www.fishersci.com/trademarks).

### In the United States:

For customer service, call 1-800-766-7000  
To fax an order, use 1-800-926-1166  
To order online: [www.fishersci.com](http://www.fishersci.com)

BN1114161



**Fisher  
Scientific**

A Thermo Fisher Scientific Brand

© 2016 Sonoco ThermoSafe