

# Envoy<sup>®</sup>

## Pre-Qualified Insulated Shipper Series

### **SIMPLE SOLUTIONS** with Economic Convenience

*Numerous configurations available to meet virtually any need*

The Envoy Series, supplied by Sonoco ThermoSafe, features a vast selection of temperature ranges, utilizing standardized materials with the lowest packaging cost available. These pre-qualified shippers are ideal for shipping pharmaceuticals, clinical treatments, and diagnostic samples.

- Simple packout provides fast assembly
- Pre-Qualified to our real-world ISCSilver<sup>®</sup> ambient profile
- Features **ZERO BENCH-TIME™** refrigerant design which enables you to improve your speed of pack to ship
- Manufactured in the U.S. and Europe
- Four container sizes and modular designs give you the flexibility to change refrigerants to meet your temperature criteria



#### Specifications:

- Temperature Ranges: 2-8 °C, 15-25 °C, < -20 °C
- Duration
  - Refrigerated and CRT: Minimum of 2 days
  - Frozen: Minimum of 4 days
- Packout Configuration: Seasonal
- Ambient Profile: ISCSilver
- Insulation: Expanded Polystyrene (EPS)

If one of the new ready-engineered shippers does not meet your shipping requirements, a custom solution can easily be tailored to your exact requirements.

## Available Models

Temperature Range	Product Capacity (L)	Weight lbs. [kgs]		Payload ID in. [mm]			OD in. [mm]			Part Number	
		Summer	Winter	L	W	H	L	W	H	Summer	Winter
2-8 °C	2.5	17.4 [7.9]	12.4 [5.6]	9.01 [229]	7.99 [203]	2.13 [54]	16.7 [425]	15.75 [400]	16.26 [413]	03531700	03531701
2-8 °C	6.4	23.4 [10.6]	20.8 [9.4]	8.86 [225]	7.87 [200]	5.63 [143]	16.7 [425]	15.75 [400]	21.26 [540]	03531702	03531703
2-8 °C	12.1	36.1 [16.4]	28.9 [13.1]	11.14 [283]	9.6 [244]	6.89 [175]	20.51 [521]	19.01 [483]	20.75 [527]	03531704	03531705
2-8 °C	24.1	63.3 [28.7]	43.9 [19.9]	19.76 [502]	11.26 [286]	6.61 [168]	29.02 [737]	20.51 [521]	21.26 [540]	03531706	03531707
15-25 °C	4.5	14.2 [6.4]	10.0 [4.5]	7.99 [203]	7.01 [178]	4.88 [124]	16.7 [424]	15.75 [400]	16.26 [413]	03531708	03531709
15-25 °C	7.2	19.2 [8.7]	14.2 [6.4]	7.99 [203]	7.01 [178]	7.87 [200]	16.7 [424]	15.75 [400]	21.26 [540]	03531710	03531711
15-25 °C	18.2	28.8 [13.1]	19.4 [8.8]	11.14 [283]	9.61 [244]	10.47 [266]	20.51 [521]	19.01 [483]	20.75 [527]	03531712	03531713
15-25 °C	39.6	49.8 [22.6]	32.8 [14.9]	19.76 [502]	11.26 [286]	10.87 [276]	29.02 [737]	20.51 [521]	21.26 [540]	03531714	03531715
< -20 °C	2.5	23.8 [10.8]		9.01 [229]	7.99 [203]	2.13 [54]	16.7 [424]	15.75 [400]	16.26 [413]	03531716	
< -20 °C	5.6	31.8 [14.4]		9.01 [229]	7.99 [203]	4.76 [121]	16.7 [424]	15.75 [400]	21.26 [540]	03531717	
< -20 °C	12.1	49.2 [22.3]		11.14 [283]	9.6 [244]	6.89 [175]	20.51 [521]	19.01 [483]	20.75 [527]	03531718	
< -20 °C	24.1	88.9 [40.3]		19.76 [502]	11.26 [286]	6.61 [168]	29.02 [737]	20.51 [521]	21.26 [540]	03531719	

Envoy®, ThermoSafe®, Sonoco ThermoSafe® are registered trademarks of Sonoco Products Company.  
ZERO BENCH-TIME™ is a trademark of Sonoco Products Company.



**SONOCO**  
**THERMOSAFE**

© 2014 Thermo Fisher Scientific Inc. All rights reserved.  
Trademarks used are owned as indicated at [www.fishersci.com/trademarks](http://www.fishersci.com/trademarks).

### In the United States:

For customer service, call 1-800-766-7000  
To fax an order, use 1-800-926-1166  
To order online: [www.fishersci.com](http://www.fishersci.com)

**F** **Fisher Scientific**

A Thermo Fisher Scientific Brand

BN #0806141