

Brady B-7425 Thermal Transfer Specimen Identification Labels



Economical specimen identification for the laboratory environment.

From liquid nitrogen to autoclave, B-7425 labels remain adhered to specimen containers through the toughest laboratory environments. Research, academic and clinical labs now have a durable yet economical solution for identifying vials, tubes and other specimen containers prior to being frozen. B-7425 laboratory labels are made to perform across a wide temperature range while withstanding exposure to common laboratory solvents, such as DMSO, short term Xylene, IPA and ethanol.

Features:

- Durable THT printable white polypropylene material.
- Temperature range from -196°C (-320°F) to 120°C (248°F).
- Survives exposure to common laboratory environments such as liquid nitrogen, freezer, water bath, and autoclave.
- Excellent performance when exposed to laboratory chemicals such as DMSO, short term Xylene, IPA and ethanol.
- Apply to dry specimen containers with no overlap needed. (Labels must be applied to containers prior to being frozen.)
- Label sizes are available for vials, tubes, slides, well plates and other specimen containers.
- Stock sizes available for BMP®21 portable printer and Brady benchtop OEM printers, including 1" core rolls for the BBP®11 printer.
- Custom label options available.



Brady B-7425 Thermal Transfer Specimen Identification Labels

Fisher Scientific #	Size	Core Size	Printer Compatibility
19140418	0.825" x 0.250"	3" Core	IP Printer, PR+, BBP11 w/ external feeder
19140419	1.000" x 0.375" w/ 0.375" dia top	3" Core	IP Printer, PR+, BBP11 w/ external feeder
19140420	1.000" x 0.500" w/ 0.440" dia top	3" Core	IP Printer, PR+, BBP11 w/ external feeder
19140421	1.000" x 0.375"	3" Core	IP Printer, PR+, BBP11 w/ external feeder
19140422	1.000" x 0.500"	3" Core	IP Printer, PR+, BBP11 w/ external feeder
19140423	1.000" x 0.750"	3" Core	IP Printer, PR+, BBP11 w/ external feeder
19140424	1.000" x 1.000"	3" Core	IP Printer, PR+, BBP11 w/ external feeder
19140425	1.300" x 0.600"	3" Core	IP Printer, PR+, BBP11 w/ external feeder
19140426	1.500" x 0.500"	3" Core	IP Printer, PR+, BBP11 w/ external feeder
19140427	1.500" x 0.750"	3" Core	IP Printer, PR+, BBP11 w/ external feeder
19140428	1.500" x 1.000"	3" Core	IP Printer, PR+, BBP11 w/ external feeder
19140429	1.500" x 1.750"	3" Core	IP Printer, PR+, BBP11 w/ external feeder
19140430	2.000" x 0.500"	3" Core	IP Printer, PR+, BBP11 w/ external feeder
19140431	2.000" x 0.250"	3" Core	IP Printer, PR+, BBP11 w/ external feeder
19140432	2.000" x 1.000"	3" Core	IP Printer, PR+, BBP11 w/ external feeder
19140433	0.825" x 0.250"	1" Core	BBP11 only
19140434	1.000" x 0.375" w/ 0.375" dia top	1" Core	BBP11 only
19140435	1.000" x 0.500" w/ 0.440" dia top	1" Core	BBP11 only
19140436	1.000" x 0.375"	1" Core	BBP11 only
19140437	1.000" x 0.500"	1" Core	BBP11 only
19140438	1.000" x 0.750"	1" Core	BBP11 only
19140439	1.000" x 1.000"	1" Core	BBP11 only
19140440	1.300" x 0.600"	1" Core	BBP11 only
19140441	1.500" x 0.500"	1" Core	BBP11 only
19140442	1.500" x 0.750"	1" Core	BBP11 only
19140443	1.500" x 1.000"	1" Core	BBP11 only
19140444	1.500" x 1.750"	1" Core	BBP11 only
19140445	2.000" x 0.500"	1" Core	BBP11 only
19140446	2.000" x 0.250"	1" Core	BBP11 only
19140447	2.000" x 1.000"	1" Core	BBP11 only
19140448	0.375" x 21"	Cartridge	BMP21
19140449	0.500" x 21"	Cartridge	BMP21
19140450	0.750" x 21"	Cartridge	BMP21



BN#0121152

© 2015 Brady Worldwide Inc. ALL RIGHTS RESERVED

In the United States:

For customer service, call 1-800-766-7000
To fax an order, use 1-800-926-1166
To order online: www.fishersci.com

In Canada:

For customer service, call 1-800-234-7437
To fax an order, use 1-800-463-2996
To order online: www.fishersci.ca