

Isotemp™ Refrigerators and Freezers

Flammable Material Laboratory Refrigerators and Freezers

Isotemp Flammable Material Storage Refrigerators, Freezers and Combination Units

Isotemp™ flammable material storage laboratory refrigerators and freezers are available in sizes from undercounter to full-height freestanding.

- Spark-free interior to reduce the risk of internal explosion
- All models feature manual defrost
- Tough white exterior (except model number 50FREEFSA)
- CFC- and HCFC-free refrigeration system and insulation
- Designed to meet NFPA 45 and 99 along with OSHA article 1910.307



05FREEFSA Refrigerator



05FFEEFSA Freezer



50FREEFSA Refrigerator



10FCEEFS Refrigerator-Freezer



20FFEEFS Freezer



20FREEFS Refrigerator

Capacity	Interior Storage	Voltage	Exterior Dimensions (H X W X D)	Interior Dimensions (H X W X D)	Agency Listing	Shipping Weight	Cat. No.
Isotemp™ Flammable Material Refrigerators (Temperature Range 1° to 12°C)							
5.5 cu. ft. (155.7L)	3 adjustable shelves, storage on bottom	115V/60Hz	33.5" X 23.63" X 28.1" (85.1 X 61 X 71.37cm)	27.75" X 20" X 17.5" (70.5 X 50.8 X 44.5cm)	UL listed, meets NFPA 45 and 70	120 lb. (54.5kg)	05FREEFSA
20.9 cu. ft. (591.82L)	4 fixed interior shelves, 6 door shelves	115V/60Hz	73.13" X 34" X 35.81" (185.7 X 86.4 X 90.95cm)	57.8" X 27.8" X 23.8" (146.7 X 70.49 X 60.3cm)	cCSAus	198 lb. (89.8kg)	20FREEFSA
50 cu. ft. (1415.8L)	8 adjustable shelves	115V/60Hz	77.25" X 52" X 34.25" (196.2 X 132.1 X 87cm)	59" X 45.75" X 26.5" (149.8 X 116.2 X 67.3cm)	UL	420 lb. (190.5kg)	50FREEFSA
Isotemp™ Flammable Material Freezers (Temperature Range -12° to -20°C)							
5.0 cu. ft. (141.6L)	2 fixed interior, 1 bottom tray, 3 door shelves	115V/60Hz	33.13" X 21.38" X 25.75" (84.15 X 54.3 X 65.4cm)	29.5" X 18.63" X 19" (74.9 X 47.32 X 48.2cm)	UL listed, meets NFPA 45 and 70	95 lb. (43kg)	05FFEEFSA
20.9 cu. ft. (591.82L)	4 fixed shelves, 6 door shelves	115V/60Hz	73.13" X 34" X 35.81" (185.7 X 86.4 X 90.95cm)	57.8" X 27.8" X 23.8" (146.7 X 70.49 X 60.3cm)	cCSAus	198 lb. (89.8kg)	20FFEEFSA
Isotemp™ Flammable Material Combination Refrigerator/Freezers† (Temperature Range: 1° to 12°C [Ref], -12° to -20°C [Frz])							
10.1 cu. ft. (286L)	3 adjustable interior shelves, 1 fixed interior shelf, 1 drawer, 4 door shelves	115V/60Hz	59.75" X 23.63" X 28.6" (151.77 X 60 X 76.2cm)	Ref: 38.25" X 19.75" X 18.25" (97.2 X 50.2 X 46.4cm); Frz: 11.25" X 18" X 18.25" (28.6 X 45.7 X 46.4cm)	UL listed, meets NFPA 45 and 70	150 lb. (68kg)	10FCEEFS

© 2016 Thermo Fisher Scientific Inc. All rights reserved.
Trademarks used are owned as indicated at www.fishersci.com/trademarks.

In the United States:

For customer service, call 1-800-766-7000
To fax an order, use 1-800-926-1166
To order online: www.fishersci.com

In Canada:

For customer service, call 1-800-234-7437
To fax an order, use 1-800-463-2996
To order online: www.fishersci.ca



A Thermo Fisher Scientific Brand