

# Isotemp™ Refrigerators and Freezers

Value Laboratory Refrigerators and Freezers

## Isotemp Value Lab Refrigerators, Freezers and Combination Units

Isotemp™ Value laboratory refrigerators, freezers and combination units are particularly suited for routine laboratory applications with sizes ranging from small benchtop to full-height freestanding. Our features are not available in domestic models and meet the demanding requirements of the laboratory environment.

**Alert:** These units are not intended for critical lab samples. Storage of high-value life science materials or clinical biologicals may require alarm, monitoring, back-up and temperature performance features. The need to add these features should be determined by your industrial hygienist or safety officer. These units are not suitable for corrosive environments.

- Factory-tested prior to shipment
- NRTL-listed
- Environmentally friendly, non-CFC refrigerants
- Adjustable temperature control
- Easy-to-clean, durable finish
- Manual and auto defrost combination units
- Manual defrost refrigerators and freezers



05LFEFSA Lab Freezer



05LREEFSA Lab Refrigerator



18LCEEFS Refrigerator-Freezer



20LFEFSA Lab Freezer

Capacity	Interior Storage	Voltage	Exterior Dimensions (H X W X D)	Interior Dimensions (H X W X D)	Agency Listing	Shipping Weight	Cat. No.
<b>Isotemp™ Value Lab Refrigerators (Temperature Range 1° to 12°C)</b>							
5.5 cu. ft. (155.7L)	3 adjustable shelves, storage on bottom	115V/60Hz	33.5" X 23.63" X 23.5" (85.1 x 60 x 61cm)	27.75" X 20" X 17.5" (70.5 X 50.8 X 44.5cm)	cULus	100 lb. (45.3kg)	<b>05LREEFSA</b>
<b>Isotemp™ Value Lab Freezers (Temperature Range -12° to -20°C)</b>							
5.0 cu. ft. (141.6L)	2 fixed interior shelves, 1 bottom tray, 3 door shelves	115V/60Hz	33.13" X 21.38" X 25.75" (84.15 X 54.3 X 65.4cm)	29.5" X 18.63" X 19" (74.9 X 47.32 X 48.2cm)	cCSAus	95 lb. (43kg)	<b>05LFEFSA</b>
20.9 cu. ft. (591.82L)	4 fixed shelves, 6 door shelves	115V/60Hz	73.13" X 34" X 32.13" (185.7 X 86.4 X 81.6cm)	57.8" X 27.8" X 23.8" (146.7 X 70.49 X 60.3cm)	cCSAus	198 lb. (89.8kg)	<b>20LFEFSA</b>
<b>Isotemp™ Value Combination Lab Refrigerator/Freezers (Temperature Range: 1° to 12°C [Ref], -12° to -20°C [Frz])</b>							
5.6 cu. ft. (158.6L)	2 adjustable shelves, 1 drawer, 3 door shelves	115V/60Hz	33.5" X 23.63" X 23.5" (85.1 X 64.8 X 61cm)	Ref: 19.5" X 20.5" X 17" (49.5 X 52.1 X 43.2cm), Frz: 5" X 19" X 11.5" (12.7 X 48.3 X 29.2cm)	cULus	120 lb. (54.5kg)	<b>05LCEEFS</b>
18.0 cu. ft. (515.4L)	Ref: 2 adjustable shelves, 1 fixed shelf, 2 drawers, 3 door shelves; Frz: 1 adjustable shelf, 2 door shelves	115V/60Hz	66.63" X 30" X 30.13" (169.24 X 76.2 X 76.5cm)	Frz : 15.5" X 26.0" X 21.0" (39.4 X 66.04 X 53.34cm); Ref: 39.75" X 26.0" X 24.75" (100.9 X 66.04 X 62.86cm)	cCSAus	205 lb. (93kg)	<b>18LCEEFS</b>

© 2016 Thermo Fisher Scientific Inc. All rights reserved.  
Trademarks used are owned as indicated at [www.fishersci.com/trademarks](http://www.fishersci.com/trademarks).

### In the United States:

For customer service, call 1-800-766-7000  
To fax an order, use 1-800-926-1166  
To order online: [www.fishersci.com](http://www.fishersci.com)

### In Canada:

For customer service, call 1-800-234-7437  
To fax an order, use 1-800-463-2996  
To order online: [www.fishersci.ca](http://www.fishersci.ca)



A Thermo Fisher Scientific Brand