

Discover. Synthesize. Analyze. Customize.

# AcroSeal 25mL Packaging

Introducing a 25mL pack size to the industry-leading AcroSeal™ packaging range. These new products facilitate applications requiring small research-scale quantities of extra dry solvents.

Designed for your convenience, each bottle is packed using a new septum to ensure optimum performance for moisture-sensitive work. The new 25mL package size expands the AcroSeal portfolio to better meet your chemistry needs.




## Highlights

- Convenience:**  
 Ideal for use when requiring small quantities
- Easy to use:**  
 Extract solvent easily with a standard needle
- Quality:**  
 Water content guaranteed at less than 50 parts per million

## Discover the new products available in AcroSeal 25mL packaging

Product code	Product name	Pack size	CAS no.
448391000	Acetonitrile, 99.9%, Extra Dry	4 x 25mL	75-05-8
448371000	Dichloromethane, 99.9%, Extra Dry, stabilized	4 x 25mL	75-09-2
448421000	Diethyl ether, 99.5%, Extra Dry, stabilized	4 x 25mL	60-29-7
448381000	N,N-Dimethylformamide, 99.8%, Extra Dry	4 x 25mL	68-12-2
450171000	1,4-Dioxane, 99.8%, Extra Dry, stabilized	4 x 25mL	123-91-1
448411000	Methanol, 99.9%, Extra Dry	4 x 25mL	67-56-1
448361000	Tetrahydrofuran, 99.85%, Extra Dry, stabilized	4 x 25mL	109-99-9
448401000	Toluene, 99.85%, Extra Dry	4 x 25mL	108-88-3

## How to open the AcroSeal 25mL septum



## Related Resources



### AcroSeal product range overview

This brochure lists 600+ AcroSeal products, including solvents, reagents in solution, organics, organometallics and deuterated solvents.

Download the PDF at [www.fishersci.com/acroseal](http://www.fishersci.com/acroseal)



### AcroSeal video

This video highlights how to use AcroSeal's unique packaging to keep air- and moisture-sensitive solvents and reagents drier for extended storage.

View the video at [www.fishersci.com/acroseal](http://www.fishersci.com/acroseal)



© 2013 Thermo Fisher Scientific Inc. All rights reserved.  
 Trademarks used are owned as indicated at [www.fishersci.com/trademarks](http://www.fishersci.com/trademarks).

### In the United States:

For customer service, call 1-800-766-7000  
 To fax an order, use 1-800-926-1166  
 To order online: [www.fishersci.com](http://www.fishersci.com)

13\_1925 JA/JG 12/13 BN1217134

### In Canada:

For customer service, call 1-800-234-7437  
 To fax an order, use 1-800-463-2996  
 To order online: [www.fishersci.ca](http://www.fishersci.ca)



Part of Thermo Fisher Scientific