

# Disinfectants

*Comprehensive Product Information*



## DISINFECTANTS

### Conflikt®

#### Ready-to-use Disinfectant Spray

Conflikt® disinfects and cleans hard surfaces that may harbor viruses, bacteria, and fungi. Pre-diluted, stable solution of dual quaternary ammonium active ingredients is effective against TB, HIV-1, E-coli, and other pathogenic organisms. Conforms to OSHA's Bloodborne Pathogens Standard. EPA registered.



### Iradecon®

#### Ready-to-use Bleach Spray

Iradecon® is a pre-diluted, stabilized bleach (sodium hypochlorite) solution used to disinfect hard surfaces in labs and production areas. This ready-to-use solution is made up of 0.525% sodium hypochlorite (1:10 bleach solution) which is the strength recommended by CDC and OSHA for inactivating HIV, HBV and other pathogens. IRADECON is a safer and more convenient alternative to mixing your own bleach solutions since self made solutions are inherently unstable – often losing efficacy in 24 to 48hrs. Since IRADECON is pre-mixed and stable there are no issues with efficacy or performance. Packaged in a ready-to-use 32oz. trigger spray bottle. EPA registered. Meets OSHA's Bloodborne Pathogens Standard.



### CiDecon®

#### Concentrated Phenolic Disinfectant

CiDecon® is a concentrated germicidal cleaner for disinfecting surfaces in lab production areas and on process equipment. Diluted one ounce per gallon of water (1:128), CiDecon is effective against a wide range of pathogenic organisms including TB, HIV-1, bacteria, viruses, and fungi. Conforms to OSHA's Bloodborne Pathogens Standard. EPA registered.



### LopHene®

#### Concentrated Phenolic Germicide for Rotational Disinfection

LopHene® is used alone or used with CiDecon in a rotational disinfection program. LopHene is a concentrated low-pH germicidal cleaner for use in labs, production areas, and on process equipment. Diluted half ounce per gallon of water (1:256), LopHene is effective against a wide range of bacteria, viruses, and fungi, including TB and HIV-1. Conforms to OSHA's Bloodborne Pathogens Standard. EPA registered.



### BDD™

#### Concentrated Quaternary Ammonium Detergent Disinfectant

BDD (Bacdown® Detergent Disinfectant) will safely and effectively clean and disinfect surfaces in labs, production areas, and process equipment. Diluted two ounces per gallon of water (1:64), BDD is bactericidal, virucidal, fungicidal, effective against HIV-1, HBV, and more. Conforms to OSHA's Bloodborne Pathogens Standard. EPA registered.



### CiDecon® Wipes

#### Surface Disinfectant Wipes

CiDecon® Wipes are hard surface disinfectant wipes that provide broad-spectrum efficacy against bacteria, fungi and viruses including HIV-1. Convenient canister dispenses 65 pre-moistened wipes (6" x 10.5"). Conforms to OSHA's Bloodborne Pathogens Standard and is EPA registered.



### SporGon®

#### Sporicidal Disinfectant

SporGon® is a ready-to-use peracetic acid/hydrogen peroxide-based high-level disinfectant and sterilant. Completely effective against spores as well as being tuberculocidal, bactericidal, virucidal and fungicidal. Used at room temperature (20° C), high-level disinfection is achieved in 15 minutes and sterilization is achieved in 3 hours. Has FDA 510K clearance and conforms to OSHA's Bloodborne Pathogens Standard.



### CiDecon® Plus Wipes

#### Surface Disinfectant Wipes

CiDecon® Plus Wipes are pre-moistened hard surface disinfectant wipes for use on hard surfaces. CiDecon Plus Wipes, which come in a convenient "pop-up" canister, are economical, durable and display superior efficacy against a broad range of pathogenic organisms. Achieves hospital disinfection in 10 minutes and maintains continual residual bacteriostatic activity for up to 6 months (see label for details). FDA compliant for use on medical equipment and instruments. Conforms to OSHA's Bloodborne Pathogens Standard. EPA registered.



## PRODUCT GUIDE

PRODUCT	SIZE	FISHER SCIENTIFIC CAT. #	CASE SIZE
<b>Conflikt® Spray Disinfectant</b>	16 oz. Pump Spray	04-355-33	12 x 16 oz.
	32 oz. Trigger Spray	04-355-34	6 x 32 oz.
	64 oz. Refill	04-355-35	6 x 64 oz.
	1 gal. Refill	04-355-2	4 x 1 gal.
<b>CiDecon® Concentrate Germicidal Cleaner</b>	1 gal.	04-355-64	4 x 1 gal.
<b>LopHene® Concentrate Rotational Disinfectant</b>	1 gal.	04-355-70	4 x 1 gal.
<b>SporGon® Sporicidal Disinfectant</b>	1 gal.	04-355-72	4 x 1 gal.
<b>IRADECON® Bleach Spray Disinfectant</b>	32 oz. Trigger Spray	04-355-150	12 x 32 oz.
<b>BDD™ Bacdown Detergent Disinfectant</b>	5 Liters	04-355-13	4 x 5 L
	115 Liters	04-355-38	EACH
<b>CiDecon® Wipes Surface Disinfectant Wipes</b>	65 Wipe Canister	04-355-82	6 x 65 Wipes
<b>CiDecon® Plus Wipes Surface Disinfectant Wipes</b>	180 Wipe Canister	04-355-87	12 x 180 Wipes

Not all products are available in Canada.

## QUICK REFERENCE CHART

Quick Reference Chart	Ready-To-Use	Concentrate	Quat	Phenolic	Peracetic Acid/ Hydrogen Peroxide	Sodium Hypochlorite	Sterilant/Sporicidal	OSHA Bloodborne Pathogens Standard	Sterile, Cleanroom Packaging	EPA Registered	FDA 510K
	<b>Conflikt®</b>	●		●					●		●
<b>CiDecon® Concentrate</b>		●		●				●		●	
<b>LopHene® Concentrate</b>		●		●				●		●	
<b>SporGon®</b>	●				●		●	●			●
<b>IRADECON® Spray</b>	●					●		●		●	
<b>BDD™</b>		●	●					●		●	
<b>CiDecon® Wipes</b>	●			●				●		●	
<b>CiDecon® Plus Wipes</b>	●			●				●		●	



© 2015 Thermo Fisher Scientific Inc. All rights reserved.  
Trademarks used are owned as indicated at [www.fishersci.com/trademarks](http://www.fishersci.com/trademarks).

**In the United States:**

For customer service, call 1-800-766-7000  
To fax an order, use 1-800-926-1166  
To order online: [www.fishersci.com](http://www.fishersci.com)

**In Canada:**

For customer service, call 1-800-234-7437  
To fax an order, use 1-800-463-2996  
To order online: [www.fishersci.ca](http://www.fishersci.ca)



A Thermo Fisher Scientific Brand  
BN0203157