

Sterile Alcohol Sterile Disinfectants Sterile Water

Comprehensive Product Information

70% **Medical Device** **Research** **Phenolic** **Alcohol** **70%** **EtOH**
Process Equipment **Low pH** **Pathogens** **Sterile** **Sterile Water**
Biotechnology **Disinfectants** **Broad-Spectrum** **Alcohol**
Wipes **IPAs** **Laboratory** **Sprays** **Pharmaceutical** **70%**
Healthcare **Disinfectants** **Wipes** **Cleanroom** **Process Equipment** **IPA**
Pathogens **EtOH** **Ready-to-use** **Water** **EtOH**
Purified Water



STERILE ALCOHOL

CiDehol® ST

Sterile 70% Isopropyl Alcohol



CiDehol® ST is a ready-to-use 70% IPA solution in non-aerosol trigger spray and one gallon bottles. It is filtered to 0.2 µm, individually double-bagged and gamma-irradiated. Each lot is tested for bacterial endotoxin and sterility. Each case is shipped with a Lot Specific Document detailing parameters of QC, irradiation, endotoxin and sterility testing. Made with WFI. EPA registered.

Hands-Free Infrared Dispenser

For use with CiDehol®ST



CiDehol® ST is also available in a 32 oz. dispensing bag that is used with our hands-free infrared dispenser. The dispenser is activated by movement and can be set to dispense 1, 3 or 5 mL. The dispenser easily mounts to the wall using screws or adhesive sponge. Unit can be powered with batteries or AC adapter.

Sanihol® ST

Sterile 70% Denatured Ethyl Alcohol



Sanihol® ST is a ready-to-use 70% Ethanol solution in non-aerosol trigger spray and one gallon bottles. It is filtered to 0.2 µm, individually double-bagged and gamma-irradiated. Each lot is tested for bacterial endotoxin and sterility. Each case is shipped with a Lot Specific Document detailing parameters of QC, irradiation, endotoxin and sterility testing. Made with WFI. EPA registered.

CiDehol® ST 99

Sterile 99% Isopropyl Alcohol



CiDehol® ST 99 is a ready-to-use 99% IPA solution in non-aerosol trigger spray and one gallon bottles. It is filtered to 0.2 µm, individually double-bagged and gamma-irradiated. Each lot is tested for bacterial endotoxin and sterility. Each case is shipped with a Lot Specific Document detailing parameters of QC, irradiation, endotoxin and sterility testing.

STERILE DISINFECTANTS

CiDecon® ST

Sterile Concentrated Phenolic Disinfectant



CiDecon® ST is a sterile concentrated phenolic disinfectant. Product is individually double-bagged, gamma-irradiated, and tested to ensure sterility. Diluted at a ratio of one ounce per gallon (1:128), CiDecon provides broad spectrum efficacy against a wide variety of organisms in the cleanroom environment. 2 oz. SinglServ™ is pre-measured to make 2 gallons of working solution at the correct dilution. Conforms to OSHA's Bloodborne Pathogens Standard. Each case is shipped with a Lot Specific Document detailing parameters of QC, irradiation, and sterility. EPA registered.

LopHene® ST

Sterile Concentrated Low pH Disinfectant



LopHene® ST is a sterile, low pH acidic detergent for cleanroom use. Concentrated formula is effective against a broad range of bacteria, viruses and fungi. LopHene ST can be used alone or rotated with CiDecon ST. Dilution ratio: 1:256. 1 oz. SinglServ™ is pre-measured to make 2 gallons of working solution at the correct dilution. Conforms to OSHA's Bloodborne Pathogens Standard. Each case is shipped with a Lot Specific Document detailing parameters of QC, irradiation, and sterility. EPA registered.

STERILE WATER



AquaPur™ ST

Purified Water USP Grade



AquaPur™ ST is sterile purified water for use in dilution of sterile disinfectants, manufacturing, general laboratory and cleanroom applications. Purified water is filtered to 0.2 µm, irradiated to a SAL 10⁻⁶ and tested for sterility and endotoxin using current USP method. Meets USP and CAPS/NCCL Type I spec. Each case is shipped with a Lot Specific Document. Not for parenteral use. Not for injection, irrigation or infusion.

PRODUCT GUIDE

PRODUCT		SIZE	FISHER SCIENTIFIC CAT. #	CASE SIZE
CiDehol® ST 70% Sterile 70% IPA		16 oz. Trigger Spray	04-355-58	12 x 16 oz.
		32 oz. Trigger Spray	04-355-85	12 x 32 oz.
		1 gal. Refill	04-355-80	4 x 1 gal.
		32oz. Bag for Dispenser	04-356-15	8 x 32 oz.
		Hands-free infrared Dispenser	04-356-16	EACH
Sanihol® ST 70% Sterile Denatured Ethanol		16 oz. Trigger Spray	04-355-58	12 x 16 oz.
		1 gal.	04-355-58	4 x 1 gal.
CiDehol® ST 99% Sterile IPA		16 oz. Trigger Spray	04-355-56	12 x 16 oz.
		1 gal.	04-355-54	4 x 1 gal.
CiDecon® ST Sterile Phenolic Disinfectant		2 oz.	04-355-120	24 x 2 oz.
LopHene® ST Sterile Phenolic Disinfectant		1 oz.	04-355-127	24 x 1 oz..
AquaPur™ ST Sterile Water		1 gal.	22-281-500	4 x 1 gal.



© 2015 Thermo Fisher Scientific Inc. All rights reserved.
Trademarks used are owned as indicated at www.fishersci.com/trademarks.

In the United States:

For customer service, call 1-800-766-7000
To fax an order, use 1-800-926-1166
To order online: www.fishersci.com

In Canada:

For customer service, call 1-800-234-7437
To fax an order, use 1-800-463-2996
To order online: www.fishersci.ca



A Thermo Fisher Scientific Brand
BN0203158