



Thermo Scientific
mySPIN Mini Centrifuge Series

Fits in.
Stands out.

Thermo
SCIENTIFIC


Introducing the NEW! Thermo Scientific™ mySPIN™ 12 and 6 mini centrifuges

Fits in.

- To your space, with its compact footprint
- To your applications, with its flexibility
- To your timeline, with quick-spin options

Stands out.

- Standard safety features provide assurance
- Efficient and easy to use with ergonomic design, duplicate spin function and tool-free rotors





mySPIN 12 mini centrifuge

- Compact design
- Easy to operate
- Quiet operation, low vibration
- Tool-free, quick rotor exchange
- Quick-spin feature
- Safety features: imbalance and tilt safety cut-out; safety interlock lid prevents opening while rotor is turning
- Able to perform fast spins with higher RCF requirements up to 9,800 x g
- Back-lit, customizable display can be set for rpm or RCF



mySPIN 6 mini centrifuge

- Compact design
- Easy to operate
- Quiet operation, low vibration
- Tool-free, quick rotor exchange
- Quick-spin feature
- Safety features: unit will not operate without lid in place
- Palm-shaped lid for left- or right-handed users
- Quick tube extraction

Packed with possibilities, the Thermo Scientific mySPIN 12 mini centrifuge is designed to give you maximum speed and flexibility in a minimized footprint.

Its compact, ergonomic design fits on any workstation and is comfortable and easy for anyone to operate. Safety features help ensure it will not operate when the lid is open, a rotor is jammed, or the unit is out of balance. Ideal for most protocols requiring fast spins (12,500 rpm / 9,800 x g), and appropriate for PCR, microfilter cell separation, and HPLC protocols.

Bring efficiency and user comfort to your lab stations with the Thermo Scientific mySPIN 6 mini centrifuge.

Ergonomic design, tool-free rotors, and quick-spin options make it fast and easy to use. Efficient, compact footprint fits into a variety of workstations. Ideal for microfilter cell separations and HPLC samples, with adapters to accommodate all major microtube and PCR tube styles (2.0, 1.5, 0.5, 0.2 mL) for customized use.

Consistent, reproducible pipetting is finally here.

The Thermo Scientific™ ClipTip™ pipetting system locks tips firmly in place – designed to prevent tips from loosening or falling off, regardless of application pressure. Try it for yourself at www.thermoscientific.com/clipTip.



Thermo Scientific mySPIN Mini Centrifuge Series

Specifications	mySPIN 12 Mini Centrifuge	mySPIN 6 Mini Centrifuge
Max Capacity	12 x 2 mL	6 x 2 mL
Max Speed	12,500 rpm (100 rpm increments)	6,000 rpm (no speed adjustments available)
Max RCF	9,800 x g (100 x g increments)	2,000 x g (no g-force adjustments available)
Timer	1 second to 30 minutes (1 second increments) and quick-spin available	n/a
Noise Level	51-53 dBA	51-53 dBA
Power	110-240 V, 50-60 Hz with 4 interchangeable plug adapters	110-240 V, 50-60 Hz with 4 interchangeable plug adapters
Dimensions (D x W x H)	20.3 x 17.1 x 11.4 cm (8 x 6.7 x 4.4 in.)	15.3 x 12.8 x 10.4 cm (6 x 5 x 4.1 in.)
Weight	1.41 kg (3.1 lbs.)	0.74 kg (1.6 lbs.)
Certifications	CE, CSA, UL	CE, CSA, UL
Warranty ¹	2 years	2 years

¹ Subject to the Thermo Fisher Scientific standard limited warranty. See thermoscientific.com or your sales representative for details.

Ordering Information

Thermo Scientific mySPIN 12 Mini Centrifuge	
Cat. No.	Description
75004081	mySPIN 12 mini centrifuge <i>Includes:</i> <ul style="list-style-type: none"> • 12 x 1.5/2.0 mL tube rotor • 32 x 0.2 mL tube rotor (singles or 4 x 8 strip) • 0.2 mL tube adapters (set of 12) • 0.5 mL tube adapters (set of 12) • Universal power adapter 110-240V 50/60 Hz, with 4 interchangeable plug types

Replacement Parts	
75004083	12 x 1.5/2.0 mL tube rotor
50144572	Rotor cover for 12 x 1.5/2.0 mL tube rotor (75004083)
75004084	32 x 0.2 mL tube rotor (singles or 4 x 8 strip)
50144571	Rotor knob
50146145	Tube adapter inserts for 0.2/0.5 mL (12 per pack; 6 of each size)
75004082	Power adapter
20190362	Universal power cord

Thermo Scientific mySPIN 6 Mini Centrifuge	
Cat. No.	Description
75004061	mySPIN 6 mini centrifuge <i>Includes:</i> <ul style="list-style-type: none"> • 6 x 1.5/2.0 mL tube rotor • 16 x 0.2 mL tube rotor (singles or 2 x 8 strip) • 0.2 mL tube adapters (set of 6) • 0.5 mL tube adapters (set of 6) • Storage case for rotors and adapters • Tube rack • Universal power adapter 110-240V 50/60 Hz, with 4 interchangeable plug types

Replacement Parts	
75004062	6 x 1.5/2 mL circular rotor
75004063	16 x 0.2 mL tube rotor (singles or 2 x 8 strip)
20290729	Replacement O-ring
50146145	Tube adapter inserts for 0.2/0.5 mL (12 per pack; 6 of each size)
75004064	Power adapter and universal power cord set

thermoscientific.com/centrifuge

© 2014 Thermo Fisher Scientific Inc. All rights reserved. All trademarks are the property of Thermo Fisher Scientific Inc. and its subsidiaries. Specifications, terms and pricing are subject to change. Not all products are available in all countries. Please consult your local sales representative for details.

Australia +61 39757 4300
Austria +43 1 801 40 0
Belgium +32 53 73 42 41
China +800 810 5118 or +400 650 5118
France +33 2 2803 2180
Germany national toll free 0800 1 536 376
Germany international +49 6184 90 6000

India toll free 1800 22 8374
India +91 22 6716 2200
Italy +39 02 95059 552
Japan +81 3 5826 1616
Netherlands +31 76 579 55 55
New Zealand +64 9 980 6700
Nordic/Baltic/CIS countries +358 9 3291 0200

Russia +7 812 703 42 15
Spain/Portugal +34 93 223 09 18
Switzerland +41 44 454 12 22
UK/Ireland +44 870 609 9203
USA/Canada +1 866 984 3766

Other Asian countries +852 2885 4613
Countries not listed +49 6184 90 6000

Thermo
SCIENTIFIC

A Thermo Fisher Scientific Brand