



Securing your specimens with durable identification

When it comes to specimen identification, tracking and chain of custody, you need a labeling solution that stands up to harsh lab conditions. Whether you're applying a label to a room temperature sample, or one that is already frozen, Brady offers cryo-specific label materials that survive in liquid nitrogen or ultra-low temperature freezers. With these labels in hand, you can count on crisp and durable label materials, legible text and barcoding capabilities to keep your specimen safe and secure.



FreezerBondz™ Thermal Transfer Printable Labels

Features:

- Designed to be applied to new or frozen surfaces
- Survives exposure to common laboratory environments such as liquid nitrogen, freezer (-196°C), autoclave, and water baths up to 121°C
- Excellent chemical resistance when exposed to lab chemicals such as DMSO and Xylene

Fast and incredibly simple, with a small desktop footprint and no wasted labels

BBP®33 Printer is a benchtop sized laboratory label printer with unprecedented ease of use. The BBP33 utilizes fully-automatic smart chip technology allowing the printer, ribbon, label roll and PC software to communicate. This eliminates tedious sensor adjustments, trial and error settings, and wasted blank labels from calibration. The BBP33 label printer is so incredibly easy and fast to setup that most users don't believe us the first time we show them!

- No calibration required – means no wasted blank labels!
- 20 second supply changeovers
- Automatic label setup in software – no scrolling through label lists, no burn temperatures or print speed trial and error!
- Simple to train others to use – anyone can do it!

The muscle of a benchtop printer in a small package:

- Sharp 300 dpi printing
- Fast print speed – up to 3" per second
- Over 300 label parts designed specifically for the laboratory



BBP®33
SIGN & LABEL PRINTER

BRADY 360
5 YEAR
WARRANTY

Fisher Scientific Cat #	Brady#	Description	Qty to order	Fisher Scientific Price
19-140-593	BBP33-C-LMP	BBP33 printer with Labelmark software	1	\$1,595.00
19-140-901	B33-155-492	1.625" x 0.60" Freezerbondz cryovial label, 1,500/roll ** USE ON FROZEN SURFACES **	1	\$98.99
19-140-553	B33-179-492	1.0" x 1.0" Freezerbondz cryovial label, 1,900/roll	1	\$164.01
19-140-586	B33-181-492	1.0" x 0.5" with 0.375" dia top vial label set Freezerbondz, 1,500 sets/roll	1	\$106.08
19-140-589	B30-R6400	Black printer ribbon for Freezerbondz labels, 200/roll	1	\$54.06
19-140-892	B33-158-490	3.75" x 1.5" white cryobox label, 1,000/roll	1	\$186.99
19-211-112	B30-R4300	Black printer ribbon for cryobox label, 200/roll	1	\$53.00
				\$2,258.13

For labs needing a higher volume label printing solution or 600dpi print resolution please contact local Fisher/Brady sales team

BN#0929141
© 2015 Brady Worldwide Inc. All Rights Reserved.

In the United States:
For customer service, call 1-800-766-7000
To fax an order, use 1-800-926-1166
To order online: www.fishersci.com

In Canada:
For customer service, call 1-800-234-7437
To fax an order, use 1-800-463-2996
To order online: www.fishersci.ca