



# DISPOSABLE CULTURE TUBES

## DISPOSABLE CULTURE TUBES

# PLAIN DISPOSABLE BOROSILICATE GLASS TUBES

These premium quality tubes feature sturdy, uniform bottoms and consistent lengths. The 10 x 75 and 12 x 75 mm sizes are suitable for cell washing procedures.

Three clear glass test tubes are standing upright in a row, positioned to the left of the experimental setup.

Part Number	Overflow Capacity (mL)	OD x Length (mm)	Case Qty
14-957-90E	1	6 x 50	1000
033410	4	10 x 75	1000
033411	6	12 x 75	1000
03-341-3	10	13 x 100	1000
14-961-35	13	16 x 85	1000
03-341-4	15	16 x 100	1000
033415	19	16 x 125	1000
03-341-6	23	16 x 150	1000
14-957-96J	28.5	18 x 150	500
14-957-96K	36	20 x 150	500
14-961-34	55	25 x 150	500

## PLAIN DISPOSABLE SODA-LIME GLASS TUBES



Part Number	Overflow Capacity (mL)	OD x Length (mm)	Case Qty
14-958C	6	12 x 75	1000
14-962-11	13	16 x 75	1000
22-037-511	19	16 x 125	1000

## AMBER PLAIN DISPOSABLE BOROSILICATE GLASS TUBES

These premium quality tubes are produced from amber borosilicate glass to give superior protection for light sensitive applications.



Part Number	Overflow Capacity (mL)	OD x Length (mm)	Case Qty
13-678-255	4	10 x 75	1000
13-678-256	10	13 x 100	1000
13-678-257	15	16 x 100	1000

## KIM-KAP™ POLYPROPYLENE CLOSURES

## KIM-KAP® polypropylene closures for culture tubes.

Part Number	Tube OD (mm)	Color	Case Qty
14-957-91	13	Natural	1,000
14-957-91A	16	Natural	1,000
14-957-91B	18	Natural	1,000
14-957-91C	20	Natural	500
14-957-91D	25	Natural	500
14-957-91E	38	Natural	250
14-957-92	13	Red	1,000
14-957-92D	16	Red	1,000
14-957-92H	18	Red	1,000
14-957-92M	20	Red	500
14-957-92R	25	Red	500
14-957-92A	13	Green	1,000
14-957-92E	16	Green	1,000
14-957-92J	18	Green	1,000
14-957-92N	20	Green	500
14-957-92S	25	Green	500
14-957-92B	13	Yellow	1,000
14-957-92F	16	Yellow	1,000
14-957-92K	18	Yellow	1,000
14-957-92P	20	Yellow	500
14-957-92T	25	Yellow	500
14-957-92C	13	Blue	1,000
14-957-92G	16	Blue	1,000
14-957-92L	18	Blue	1,000
14-957-92Q	20	Blue	500
14-957-92V	25	Blue	500



**Call Toll-Free: 888.546.2531**  
Customer Service hours: 8am - 5pm U.S. EST

