



9 mm Wide Opening Screw Thread Vials & Caps

Cat. No.	Description
03-391-8	9 mm wide opening screw top clear vial, no patch
03-391-9	9 mm wide opening screw top amber vial with patch
03-391-31	9 mm blue PP cap, ivory PTFE/ Red Rubber
03-391-14	9 mm blue PP cap, red PTFE/ white silicone
03-391-32	9 mm screw cap, blue PP, red PTFE/ white silicone/ red PTFE
03-391-15	Kit - 9 mm screw vial, clear no patch, blue PP cap, red PTFE/ white silicone
03-391-35	300 µL polyspring Insert, clear glass, conical, 6 × 31 mm
13-622-123	9 mm screw top vial, clear glass, fused 350 µL insert
13-622-124	9 mm wide opening screw top clear PP vial, conical 300 µL

10 mm Wide Opening Screw Thread Vials & Caps

Cat. No.	Description
03-391-16	10-425 wide opening clear vial, no patch
03-391-36	10-425 wide opening amber vial with patch
03-391-17	10-425 black PP cap, red PTFE/ white silicone
03-391-18	Kit - 10-425 wide opening clear vial, no patch, light blue cap, red PTFE/ white silicone
03-391-35	300 µL polyspring Insert, clear glass, conical, 6 × 31 mm

4 mL Screw Thread Vials & Caps

Cat. No.	Description
03-391-19	4 mL 13-425 clear vial, no patch
03-391-37	4 mL 13-425 amber vial with patch
03-391-21	13-425 screw cap, black, red PTFE/ white silicone
03-391-22	Kit - 4 mL 13-425 clear vial, no patch, black cap, red PTFE/ white silicone

Shell Vials & Caps

Cat. No.	Description
03-391-23	1 mL shell vial, clear no patch, SepCap
03-391-24	4 mL shell vial, clear no patch, SepCap

A comprehensive range of vial and closures products that meet your critical sampling needs

- 9 mm Wide Opening Screw Thread Vials and Caps
- 10 mm Wide Opening Screw Thread Vials and Caps
- 11 mm Standard and Wide Opening Crimp Thread Vials and Caps
- 8mm Standard Screw Thread Vials and Caps
- 11mm Snap Top Vials and Caps
- 4 mL Screw Thread Vials and Caps
- 1 mL & 4 mL Shell Vials and Caps
- 20 mm Crimp Top Headspace Vials and Caps
- 18 mm Screw Thread Head space Vials and Caps





11 mm Standard & Wide Opening Crimp Thread Vials & Caps

Cat. No.	Description
03-391-2	11 mm standard opening clear crimp vial, no patch
03-391-38	11 mm standard opening amber vial, no patch
03-391-5	11 mm wide opening clear crimp vial no patch
03-391-6	11 mm wide opening amber crimp with patch
03-391-3	11 mm crimp cap silver, clear PTFE/Red Rubber
03-391-33	11 mm crimp cap silver, red PTFE/ white silicone
03-391-34	11 mm crimp cap silver, red PTFE/white silicone/red PTFE
03-391-7	Kit - 11 mm wide opening clear no patch, silver cap clear PTFE/Red Rubber
03-391-4	Kit - 11 mm standard opening clear no patch, silver cap clear PTFE/Red Rubber
03-391-35	300 µL polyspring insert, clear glass, conical, 6 × 31 mm
13-622-126	11 mm wide opening crimp/snap clear vial, 250 µL fused insert
13-622-127	11 mm wide opening crimp/snap clear PP vial, 250 µL conical insert

20 mm Crimp Top HS Vials & Caps

Cat. No.	Description
13-622-128	20 mL beveled top, flat bottom, clear HeadSpace vial
13-622-129	10 mL beveled top, flat bottom, clear HeadSpace vial
13-622-130	20 mm silver crimp cap, tan PTFE/white silicone, 9.5 mm hole
13-622-131	20 mm silver pressure release crimp cap, tan PTFE/white silicone, 8.0 mm hole

8-425 Standard Opening Screw thread

Cat. No.	Description
03-391-44	8-425 screw thread vial, clear, no patch
03-391-45	8-425 screw thread vial, amber no patch
03-391-46	8-425 screw cap black PP, PTFE/silicone

Snap Top Vials

Cat. No.	Description
03-391-39	11mm snap top wide opening clear, no patch
03-391-40	11mm snap top wide opening clear, ID patch
03-391-41	11mm snap top wide opening clear, ID patch
03-391-42	11mm snap cap, red PTFE/white silicone
03-391-43	11mm snap cap, pre-slit blue PTFE/white silicone

18mm Screw Thread HS Vials & Caps

Cat. No.	Description
13-622-132	20 mL clear precision thread 18 mm screw top vial
13-622-133	20 mL amber precision thread 18 mm screw top vial
13-622-134	10 mL clear precision thread 18 mm screw top vial
13-622-135	10 mL amber precision thread 18 mm screw top vial
13-622-136	18 mm magnetic silver cap, white silicone/blue PTFE, 1.5 mm thick
13-622-137	18 mm magnetic silver cap, red butyl/grey PTFE, 1.6 mm thick

In the United States:

For customer service, call 1-800-766-7000
To fax an order, use 1-800-926-1166
To order online: www.fishersci.com