



**Fisherbrand**<sup>®</sup>  
 QUALITY. RELIABILITY. VALUE.

# Easy Reader Plastic Centrifuge Tubes

Polypropylene or PET graduated tubes are easy to read

## Key Features

- Tubes sterilized by gamma radiation
- Made of durable, chemical resistant, clear polypropylene
- With black graduations and white marking area
- Conical bottoms
- Choice of closures; plug-seal or flat top
  - Blue plug-seal closure features double-start thread design for an exceptionally tight seal
  - Flat-top caps offer faster handling and allow you to label the top of the tube
- 15 mL Tubes are graduated in 0.5 mL subdivisions from 2 to 14.5 mL
- 50 mL Tubes are graduated in 5 mL increments from 5 to 50 mL
- Certified nonpyrogenic



## Fisherbrand Centrifuge Tubes Ordering Information

Capacity	O.D. x L	Max RCF	Type	Closure	Packaging Type	Case Qty	Cat. No.
<b>Polypropylene</b>							
15 mL	17 x 119 mm	6000 x g	Sterile	Plug Seal	25/Rack	500	05-539-5
15 mL	17 x 119 mm	6000 x g	Sterile	Flat Top	25/Rack	500	05-539-12
15 mL	17 x 119 mm	6000 x g	Sterile	Plug Seal	25/Sleeve	500	05-539-4
15 mL	17 x 119 mm	6000 x g	Sterile	Flat Top	25/Sleeve	500	07-200-886
50 mL	28 x 115 mm	9400 x g	Sterile	Plug Seal	25/Rack	500	05-539-6
50 mL	28 x 115 mm	9400 x g	Sterile	Plug Seal	25/Sleeve	500	05-539-7
50 mL	28 x 115 mm	9400 x g	Sterile	Flat Top	25/Rack	500	05-539-8
50 mL	28 x 115 mm	9400 x g	Sterile	Flat Top	25/Sleeve	500	05-539-13
50 mL	28 x 115 mm	9400 x g	Nonsterile	Plug Seal	25/Sleeve	500	05-539-9
<b>Polyethylene Teraphthalate</b>							
15 mL	17 x 119 mm	1800 x g	Sterile	Plug Seal	Rack	500	05-539-1
50 mL	28 x 115 mm	1800 x g	Sterile	Plug Seal	Rack	500	05-539-10
<b>High-Speed Polypropylene</b>							
50 mL	28 x 115 mm		Sterile	Plug Seal	25/Rack	500	06-443-20
50 mL	28 x 115 mm		Sterile	Plug Seal	25/Sleeve	500	06-443-21
50 mL	28 x 115 mm		Sterile	Flat Top	25/Rack	500	06-443-18
50 mL	28 x 115 mm		Sterile	Flat Top	25/Sleeve	500	06-443-19

© 2014 Thermo Fisher Scientific Inc. All rights reserved.  
 Trademarks used are owned as indicated at [www.fishersci.com/trademarks](http://www.fishersci.com/trademarks).

### In the United States:

For customer service, call 1-800-766-7000  
 To fax an order, use 1-800-926-1166  
 To order online: [www.fishersci.com](http://www.fishersci.com)

### In Canada:

For customer service, call 1-800-234-7437  
 To fax an order, use 1-800-463-2996  
 To order online: [www.fishersci.ca](http://www.fishersci.ca)



**Fisher  
 Scientific**

A Thermo Fisher Scientific Brand