




# Fisher Scientific

**eISCO**  
Trust | Deliver | Learn

Wooden Test Tube Racks



S02635




S07854



S07855



S07856



S07857



S07853



S99371 & S99372

Part #	O.D. Tube (mm)*	Format	Number of Places
S02635	20 - 21	1 X 6	6 Hole Rack
S07854	20	1 X 6	6 Hole Rack with 6 Drying Pins
S07855	20 - 25	1 X 6, 1 X 7	13 Hole, 6 Pins, 2 Shelves
S07856	22	2 X 6	12 Tube Capacity
S07857	28	2 X 6	12 Tube Capacity
S07853	Any size	90 Pin	Can hold up to 90 pieces
S99371	11 - 19	1	1 Pin Style Holder
S99372	30	1	1 Pin Style Holder

\*O.D. indicates the maximum outer dia. of a test tube the rack can hold.



# Fisher Scientific

**eISCO**  
Trust | Deliver | Learn


## Epoxy Coated Wire Test Tube Racks

### Features:

- Manufactured in thick gauge steel wire
- Epoxy coated
- Welded joints
- Available in a variety of configurations

### Benefit

- Chemical resistance
- Temperature resilience
- Decades of use
- Low cost durable solution



Part #	O.D. Tube (mm)	Format	Number of Places	Dimensions
S13445	18 - 20	4 x 5	20	5 x 3.5 x 2.5"
S13446	15 - 16	4 x 6	24	12.5 x 4 x 2.5"
S13447	18 - 20	4 x 10	40	9.5 x 4 x 3.25"
S13448	20 - 22	4 x 10	40	10.5 x 4.5 x 3.25"
S13449	10 - 13	6 x 6	36	4.25 x 4.25 x 2.5"
S13450	15 - 16	6 x 12	72	9.5 x 5 x 2.5"
S13451	18 - 20	8 x 10	80	9.5 x 7.75 x 3.25"
S13452	22 - 25	8 x 10	80	35.5"

© 2016 Thermo Fisher Scientific Inc. All rights reserved.  
Trademarks used are owned as indicated at [www.fishersci.com/trademarks](http://www.fishersci.com/trademarks).

### In the United States:

For customer service, call 1-800-766-7000

To fax an order, use 1-800-926-1166

To order online: [www.fishersci.com](http://www.fishersci.com)