


Manufactured by



Leave no sample behind. Introducing Low Retention Tips!

While not always visible, standard pipette tips have properties that cause surface binding – in other words, droplets or a thin film of liquid often remains in the pipette tip after dispensing. In many applications, even trace amounts of missing sample can affect experimental results.

Tips with *VistaLab Low Retention Polymer Technology* are an ideal choice when working with detergents, enzymes, viscous samples, foaming liquids, plasma, TRIS, BSA and Tween.

- Improved sample accuracy
- Saves costly reagents or enzymes
- Reduced sample loss for higher reproducibility
- Unaffected by detergents used in PCR or other biological applications
- Certified for RNase/DNase and Pyrogen-free requirements

VistaLab Low Retention Tips are available in 3 different sizes for use with your Ovation and MLA pipettes.



89368-678 Catalog number

Ovation – electronic single channel and multichannel models:	0.5-20µL	2-125µL 5-250µL	25-850µL 25-1250µL
Ovation – adjustable volume models:	0.2-2µL 1.0-10µL 2.0-20µL	10-100µL 20-200µL	100-1000µL
Ovation – fixed volume models:	1µL to 20µL	21µL to 200µL	201µL to 1000µL
MLA models:		2µL to 200µL	201µL to 1000µL
	TIP SIZE:	MICRO	SMALL LARGE
VistaRak, Low Retention 192 tips/rack, 5 racks		22-146-560	22-146-564
VistaRak, Sterile, Pyrogen-free, Low Retention, RNase/DNase certified, 192 tips/rack, 5 racks		22-146-561	22-146-565
VistaRak, Filtered, Sterile, Pyrogen-free, Low Retention, RNase/DNase certified, 192 tips/rack, 5 racks		22-146-562	22-146-566

© 2015 Thermo Fisher Scientific Inc. All rights reserved.
Trademarks used are owned as indicated at www.fishersci.com/trademarks.

In the United States:

For customer service, call 1-800-766-7000
To fax an order, use 1-800-926-1166
To order online: www.fishersci.com

In Canada:

For customer service, call 1-800-234-7437
To fax an order, use 1-800-463-2996
To order online: www.fishersci.ca



A Thermo Fisher Scientific Brand

BN02041510