



Solana[®]
GAS ASSAY



Group A Strep results in an actionable time-frame. No culture confirmation required.

Today's Strep A diagnostic landscape consists of rapid tests that are fast and easy, but lack sensitivity; or culture methods that are sensitive, but complex and slow. Solana delivers results you can trust in an actionable timeframe, without the need for culture back up.

Prompt initiation of patient management and antimicrobial therapy

- Results in just 30 minutes
- High volume throughput capabilities
Batch up to 12 tests per run

No Culture Back Up

- Gold standard sensitivity
- Confidence in your prescription decision

Ease and Affordability


- Reduced hands-on time vs. culture
- Simple procedure
- Competitive reagent pricing
- Flexible instrument placement options

The Accurate. Sustainable.
Molecular **Strep** Solution.




Solana Strep Complete Assay run with the Solana benchtop instrument a mere 9.4" x 9.4" x 5.9"

Procedure



Time to 12 results



Clinical performance

Performance Results of Solana GAS Assay for Group A β -hemolytic Streptococcus

		Composite Culture			Sensitivity	98.2%
		POS	NEG	Total	Specificity	97.2%
Solana GAS	POS	220	24*	244		
	NEG	4**	833	837		
	Total	224	857	1081		

*Of the twenty-four (24) discordant specimens, sixteen (16) of these specimens were positive for GAS when tested with an additional FDA-cleared molecular device, eight (8) were negative.

**Of the four (4) discordant specimens, three (3) were negative when tested with an additional FDA-cleared molecular device.

Refer to Package Insert for additional performance claims.



Solana GAS Assay – 48 Test Kit: Cat. #23043100
 Quidel Molecular Strep A+G Control Set – 20-Reaction Kit: Cat. #23043150
 Solana GAS Startup Kit: Cat. #23043101

SSM301302EN00 (03/17)

© 2015 Thermo Fisher Scientific Inc. All rights reserved.
 Trademarks used are owned as indicated at www.fishersci.com/trademarks.

In the United States:

For customer service, call 1-800-640-0640
 To fax an order, use 1-800-290-0290
 To order online: www.fisherhealthcare.com

