

HEAVY-DUTY GLASSWARE



KIMAX® Borosilicate glassware for maximum mechanical strength and thermal shock resistance in your hard-hitting laboratory conditions.

Try these flasks and you'll become a fan for life!



KIMAX® Heavy-Duty Wide-Mouth Volumetric Flasks


- Superior strength, durability and safety from heavy, uniform walls
- Wide-mouth facilitates up to 50mL pipet access
- Quick identification with large, permanent, volume markings
- Flat interior bottoms for stirring with standard stir bars
- Accuracy - graduated to Class A volumetric tolerances
- Choose RAY-SORB® for light-sensitive compounds such as Vitamin A

KIMAX® Volumetric Flasks with Glass ⌘ Stoppers

Catalog Number	Cap. (mL)	±Tol. (mL)	⌘ Stopper	Approx. Height with Stopper (mm)	Case Qty.
13-756-684	5	0.08	13	97	6
10-310-235	10	0.08	13	100	6
10-310-236	20	0.08	13	130	6
10-310-237	25	0.08	13	130	6
K92810W-50	50	0.08	13	150	6
10-212-7A	100	0.10	16	180	6
13-756-685	200	0.20	19	223	6
10-212-7B	250	0.20	19	248	6
13-756-686	500	0.20	19	283	6
13-756-687	1000	0.30	22	335	1
13-756-688	2000	0.50	27	395	1

KIMAX® Volumetric Flasks without Stoppers

Catalog Number	Cap. (mL)	±Tol. (mL)	⌘ Stopper Size	Approx. Height without Stopper (mm)	Case Qty.
13-757-811	5	0.08	13	77	6
13-757-812	10	0.08	13	87	6
13-757-813	20	0.08	13	110	6
13-757-814	25	0.08	13	110	6
13-757-815	50	0.08	13	130	6
13-757-816	100	0.10	16	160	6
13-757-817	200	0.20	19	200	6
13-757-818	250	0.20	19	225	6
13-757-819	500	0.20	19	260	6
13-757-820	1000	0.30	22	310	1
13-757-821	2000	0.50	27	370	1



KIMAX® RAY-SORB® Volumetric Flasks with Glass ⌘ Stoppers

Choose RAY-SORB® processed flasks to protect your light-sensitive contents.



Catalog Number	Cap. (mL)	±Tol. (mL)	⌘ Stopper	Approx. Height with Stopper (mm)	Case Qty.
13-756-700	5	0.08	13	97	6
13-756-701	10	0.08	13	100	6
13-756-702	20	0.08	13	130	6
13-756-703	25	0.08	13	130	6
13-756-704	50	0.08	13	150	6
13-756-705	100	0.10	16	180	6
13-756-706	200	0.20	19	223	6
13-756-707	250	0.20	19	248	6
13-756-708	500	0.20	19	283	6
13-756-709	1000	0.30	22	335	1
13-756-710	2000	0.50	27	395	1

KIMAX® RAY-SORB® Volumetric Flasks without Stoppers


Catalog Number	Cap. (mL)	±Tol. (mL)	⌘ Stopper Size	Approx. Height without Stopper (mm)	Case Qty.
13-757-833	5	0.08	13	77	6
13-757-834	10	0.08	13	80	6
13-757-835	20	0.08	13	110	6
13-757-836	25	0.08	13	110	6
13-757-837	50	0.08	13	130	6
13-757-838	100	0.10	16	160	6
13-757-839	200	0.20	19	200	6
13-757-840	250	0.20	19	225	6
13-757-841	500	0.20	19	260	6
13-757-842	1000	0.30	22	310	1
13-757-843	2000	0.50	27	370	1

When safety is a concern, you can gain some extra yardage with heavy-duty glassware from Kimble.

KIMAX® Heavy-Duty Low Form Beakers with Double Capacity Scales

- Made from heavy-wall tubing for uniform wall thickness
- Uniformity of construction allows for use on hot plates
- Evenly tooled top rim and spout to facilitate pouring
- Durable matte finish marking area and white graduations
- Designed form ASTM Specification E960, Type II requirements

Thick, uniform walls for increased resistance to mechanical shock.



Catalog Number	Capacity (mL)	Graduated Interval (mL)	Subdivision (mL)	Approx. OD x Height (mm)	Shelf-Pack Qty.	Case Qty.
02-555-20A	250	25 to 200	25	67 x 92	12	48
02-555-20B	400	25 to 325	25	77 x 114	12	48
02-555-20C	600	50 to 500	50	87 x 122	6	36
02-555-20E	1000	100 to 1000	50	107 x 152	6	24
02-555-20G	2000	200 to 1800	200	130 x 190	4	8
02-555-20J	4000	500 to 3500	500	161 x 252	1	4



KIMAX® Heavy-Duty Solution Bottle (Carboy)

- Neck is tooled for a #12 stopper
- 5 gallon size is designed from Federal Specification DD-B-597

Catalog Number	Approx. Capacity Liters - Gallons	Approx. Dia. (mm)	Approx. Height (mm)	Case Qty.
10-310-16	9.5 - 2.5	222	392	1
10-310-17	13.2 - 3.5	257	448	1
03-422-12	19.0 - 5.0	294	502	1
03-422-12A	45.5 - 12.0	410	584	1

Carboy Clamp and Silicone Stopper Assemblies for 14950 Solution Bottles

- Two or Three-port, platinum cured stopper assembly
- Sanitary KYNAR® clamp for sterile transfer with no extractables
- Ports connect to 1/8", 1/4" (4-port stopper has two 1/4" tubes) and 3/8" with 2' silicone tubing at both ends

Catalog Number	Description	Tubing Connections	Case Qty.
03-422-18A	Clamp	-	1
03-422-18C	Stopper, 3-port	1/8"(1) 1/4"(1) 3/8"(1)	1

KYNAR is a registered trademark of ARKEMA for polyvinylidene fluoride.




Accessory Clamp and Stopper Assembly



Try KimCote plastic-coated glassware for an added measure of safety!

- Helps prevent and contain spills in the event of labware breakage
- Ultra-clear for improved sample viewing
- Non-slip surface — wet or dry
- Autoclavable and chemical resistant
- Durable and odor-free



For more information: 1-800-766-7000 • www.fishersci.com

KIMAX® Heavy-Wall Filter Flasks with Graduations

- Designed to hold 1 atmosphere of vacuum or 29 inches of mercury
- Sizes 25 - 500 mL have hose connections for 5/16-inch I.D. flexible tubing
- Sizes 1000 - 4000 mL have hose connections for 3/8-inch I.D. flexible tubing
- Designed from ASTM Specification E1406, Type II, Class I requirements



Catalog Number	Cap. (mL)	Graduated Interval (mL)	Subdiv. (mL)	Rubber Stopper Size	Approx. Widest Dia. (mm)	Approx. Height (mm)	Shelf-Pack Qty.	Case Qty.
10-181A	25	5 to 25	5	3	40	74	6	18
10-181B	50	20 to 50	10	4	48	81	6	18
10-181D	250	50 to 250	25	6	83	163	6	18
10-181E	500	150 to 500	50	7	104	190	6	18
10-181F	1000	300 to 1000	50	8	135	238	6	12
10-181G	2000	600 to 2000	100	9	168	300	—	1
10-181H	4000	1000 to 4000	250	12	208	380	—	1

KIMAX® Heavy-Duty Screw Thread Centrifuge Tubes with Caps

- Made from heavier wall tubing to withstand higher centrifuge speeds
- Choose from tapered or round bottoms
- Phenolic caps with cemented-in rubber liners (45066B) supplied but not attached



Catalog Number	Description	Capacity (mL)	O.D. x Length (mm)	GPI Thread Finish	Case Qty.
05-537	tapered bottom	40	29 x 140	24-410	12
05-558-12A	round bottom	35	29 x 100	24-410	12
05-558-12B	round bottom	50	29 x 123	24-410	12



© 2016 Thermo Fisher Scientific Inc. All rights reserved.
Trademarks used are owned as indicated at www.fishersci.com/trademarks.

In Canada:

For customer service, call 1-800-234-7437
To fax an order, use 1-800-463-2996
To order online: www.fishersci.ca



A Thermo Fisher Scientific Brand