


Wireless Remote Temperature Monitoring

From an ISO/IEC 17025 (Cert. No. 1750.01) A2LA accredited calibration laboratory



**Stay Connected—
LIVE & Secure
remote
monitoring
wherever
you go!**



15-079-615

Fisher Scientific™ TraceableLIVE™ WiFi Datalogging Refrigerator/Freezer Thermometers with Remote Notification

The simple, efficient, and reliable way to stay connected to your critical environments

- » Monitor remotely temperature and more—connect to existing WiFi
- » Alerts: temperature alarm, connectivity interruption, low battery
- » Cloud-based data interface—no local software required; web, Android, Apple IOS data visibility
- » Continuous data transmission and monitoring using SSL encrypted SECURE connection
- » Receive MOBILE PUSH / E-MAIL / TEXT notifications
- » Unlimited scalability—use TraceableLIVE™ in individual labs or an entire network of facilities
- » Multiple point temperature calibration—traceable to NIST

The TraceableLIVE™ service—Simple and SECURE setup



Purchase

Purchase a TraceableLIVE Product



Connect

Connect your new device to your existing Wi-Fi



Create

Create an account on TraceableLIVE.com




Point

Point device to your account to begin controlling device



IoT Connectivity Protect your work



Once the setup is complete you can:

- Set alarm parameters for device remotely
- View current conditions in your lab anywhere
- Generate data reports in real time
- Assign user access for the whole team



Cloud Based Secure Data Link

Traceable® Certificate

Multi-point calibration (−40°C, 0°C and 50°C) on an individually-numbered Traceable® Certificate which assures accuracy from an ISO/IEC 17025:2005 (1750.01) calibration laboratory accredited by A2LA. It indicates traceability of measurements to the SI units through NIST or other recognized national measurement institutes (NMI) that are signatories to the CIPM Mutual Recognition Agreement.

Fisher Scientific Cat. No.	Range	Accuracy	Resolution	Probes
15-079-615	−50.00 to 60.00°C (−58.00 to 140.00°F)	±0.25°C	0.01°	2 Bottles (patented)
15-079-616	−50.00 to 60.00°C (−58.00 to 140.00°F)	±0.25°C	0.01°	1 Bottle & 1 Bullet™
15-079-617	−50.00 to 60.00°C (−58.00 to 140.00°F)	±0.25°C	0.01°	2 Bullets™
15-079-618	−50.00 to 60.00°C (−58.00 to 140.00°F)	±0.25°C	0.01°	2 Stainless-steel

Traceable is a registered Trademark of Control3. TraceableLIVE™, Bullet™ are Trademarks of Control3.



Bottle Probe



Bullet™ Probe



Stainless-Steel Probe

© 2016 Thermo Fisher Scientific Inc. All rights reserved.
Trademarks used are owned as indicated at www.fishersci.com/trademarks.

In the United States:

For customer service, call 1-800-766-7000
To fax an order, use 1-800-926-1166
To order online: www.fishersci.com

In Canada:

For customer service, call 1-800-234-7437
To fax an order, use 1-800-463-2996
To order online: www.fishersci.ca



A Thermo Fisher Scientific Brand

BN1211155